


SBE

Overall Dimension




Model	L	S
1/8" BSP	22.0	11
1/4" BSP	35.0	14
3/8" BSP	38.0	17
1/2" BSP	47.0	22
3/4" BSP	57.0	27
1" BSP	73.0	34
1 1/4" BSP	83.0	43
1 1/2" BSP	93.0	51



SP

Overall Dimension




Model	L	D
1/8" BSP	5.0	06
1/4" BSP	6.0	08
3/8" BSP	7.0	10
1/2" BSP	8.0	15
3/4" BSP	9.0	20
1" BSP	10.0	26



SSA

Overall Dimension




Model	L	S
1/8" BSP	28.0	12
1/4" BSP	33.0	15
3/8" BSP	38.0	19
1/2" BSP	45.0	23
3/4" BSP	55.0	30
1" BSP	68.0	36



E

Overall Dimension




Model	L	S
1/8" BSP	29.0	13
1/4" BSP	34.0	17
3/8" BSP	37.0	22
1/2" BSP	44.0	27
3/4" BSP	53.0	32
1" BSP	65.0	41




SBM

Overall Dimension




Model	L	S
1/8" BSP	11.0	11
1/4" BSP	16.0	14
3/8" BSP	19.0	17
1/2" BSP	22.0	22
3/4" BSP	25.0	27
1" BSP	33.0	33



SDV

Overall Dimension




Model	L	S
1/8" BSP	15.0	13
1/4" BSP	20.0	16
3/8" BSP	20.0	19
1/2" BSP	22.0	24
3/4" BSP	24.0	30
1" BSP	27.0	36



PSU

Overall Dimension




Model	L	D
1/8" BSP	5.0	06
1/4" BSP	6.0	08
3/8" BSP	7.0	10
1/2" BSP	8.0	15
3/4" BSP	9.0	20
1" BSP	10.0	26



PSE

Overall Dimension



Model	L	D
1/8" BSP	29.0	13
1/4" BSP	34.0	17
3/8" BSP	37.0	25
1/2" BSP	44.0	25
3/4" BSP	53.0	37
1" BSP	65.0	48



SSM

Overall Dimension



Model	L	S
1/8" BSP	13.0	12
1/4" BSP	16.0	15
3/8" BSP	19.0	19
1/2" BSP	20.0	23
3/4" BSP	22.0	30
1" BSP	25.0	36



SVA

Overall Dimension




Model	L	S
1/8" BSP	9.5	12
1/4" BSP	11.0	15
3/8" BSP	12.5	19
1/2" BSP	13.5	23
3/4" BSP	17.0	30
1" BSP	20.5	36



SAE

Overall Dimension



Model	L	D
1/8" BSP	76	47
1/4" BSP	101	47
3/8" BSP	120	66
1/2" BSP	139	82
3/4" BSP	171	45
1" BSP	203	98



SU

Overall Dimension



Model	L	D
1/8" BSP	33.0	16
1/4" BSP	43.0	20
3/8" BSP	56.0	24
1/2" BSP	56.0	24
3/4" BSP	112.0	48
1" BSP	112.0	48

